

# STANDARD NITRILE

## X3®

### INDUSTRIAL BLUE NITRILE GLOVES



#### Recommended Uses



#### General Description

|                 |              |                 |             |
|-----------------|--------------|-----------------|-------------|
| <b>Material</b> | Nitrile      | <b>Type</b>     | Non-Sterile |
| <b>Color</b>    | Blue         | <b>Usage</b>    | Single Use  |
| <b>Shape</b>    | Ambidextrous | <b>Interior</b> | Powder Free |
| <b>Sizes</b>    | S - XXL      | <b>Exterior</b> | Textured    |
| <b>Cuff</b>     | Beaded       | <b>Process</b>  | Chlorinated |

#### Product Codes

|                 |         |
|-----------------|---------|
| <b>Small</b>    | X342100 |
| <b>Medium</b>   | X344100 |
| <b>Large</b>    | X346100 |
| <b>X-Large</b>  | X348100 |
| <b>XX-Large</b> | X349100 |

#### Packaging

|                  |                    |
|------------------|--------------------|
| <b>Box</b>       | 100 Gloves Per Box |
| <b>Box Dims</b>  | 220 x 122 x 55 mm  |
| <b>Case</b>      | 10 Boxes Per Case  |
| <b>Case Dims</b> | 298 x 258 x 240 mm |









#### Physical Properties

|                                |              |
|--------------------------------|--------------|
| <b>Tensile Strength</b>        | 14 Mpa (min) |
| <b>Tensile Strength (Aged)</b> | 14 Mpa (min) |
| <b>Powder Content</b>          | < 2 mg       |
| <b>FDA Listing</b>             | N/A          |
| <b>Elongation</b>              | 500%         |
| <b>Elongation (Aged)</b>       | 400%         |
| <b>Protein Content</b>         | N/A          |
| <b>AQL Level</b>               | 4.0          |

#### Dimensions

|                  |             |                 |            |
|------------------|-------------|-----------------|------------|
| <b>Weight</b>    | 4.2 ± 0.2 g | <b>Length</b>   | 240 ± 5 mm |
| <b>Thickness</b> |             | <b>Width</b>    |            |
| <b>Cuff</b>      | 3 ± 1 mil   | <b>Small</b>    | 85 ± 5 mm  |
| <b>Palm</b>      | 3 ± 1 mil   | <b>Medium</b>   | 95 ± 5 mm  |
| <b>Finger</b>    | 4 ± 1 mil   | <b>Large</b>    | 106 ± 5 mm |
|                  |             | <b>X-Large</b>  | 116 ± 5 mm |
|                  |             | <b>XX-Large</b> | 126 ± 5 mm |

#### Barcodes

|  |  |  |  |  |
|--|--|--|--|--|
| <br>6 97383 94085 8<br>S Box  | <br>6 97383 94096 4<br>M Box  | <br>6 97383 94107 7<br>L Box  | <br>6 97383 94118 3<br>XL Box  | <br>6 97383 94129 9<br>XXL Box  |
| <br>6 97383 94151 0<br>S Case | <br>6 97383 94162 6<br>M Case | <br>6 97383 94173 2<br>L Case | <br>6 97383 94184 8<br>XL Case | <br>6 97383 94195 4<br>XXL Case |

